

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

M52055P

3-Channel Analog Switch

REJ03F0083-0100Z

Rev.1.0

Sep.22.2003

Description

The M52055 is semiconductor integrated circuit for electronic switches used in VCR, AUDIO signal processing applications. It contains three channel two input switch circuits with each switch is controlled independently.

Features

- Low offset voltage at output: Typ. 5 mV UNDER
- Low switching noise
- Wide dynamic range
- Wide frequency range: Typ. 40 MHz OVER
- Low crosstalk
- High speed response: Typ. 0.2 μ s UNDER
- Low power consumption


Application

- VCR, AUDIO, and other applications


Recommended Operating Condition

- Supply voltage range: 4.5 to 13 V

Block Diagram



Pin Configuration




Absolute Maximum Rating

(Unless otherwise noted, $T_a = 25^\circ\text{C}$)

Symbol	Item	Rated	Units
Vcc	Supply voltage	14	V
Pd	Power dissipation	1000	mW
Topr	Operating ambient temperature	-20 to 75	$^\circ\text{C}$
Tstg	Storing temperature	-40 to 125	$^\circ\text{C}$
$k\theta$	Thermal derating	10	$\text{mW}/^\circ\text{C}$

Thermal Derating Curve



Electrical Characteristics

(unless otherwise noted, the ambient temperature (T_a) = 25°C, power supply voltage (V_{cc}) = 9 V, and current direction = current flowing into the IC is “+”)

No.	Measurement item	Symbol	Measurement conditions	Limits			Unit
				Min.	Typ.	Max.	
1	Circuit current 1	I_{CC1}	No signal input. Measure the current flowing into pin 13 .	5.2	7.1	9.0	mA
2	Circuit current 2	I_{CC2}	No signal input. Measure the current flowing into pin 13 with $V_{cc} = 5$ V.	2.4	3.4	4.4	mA
3	S1 frequency characteristics	F_{1A}	Input: 0.5-Vpp sine wave (SG1).	-0.6	-0.1	0.4	dB
4	1A, 1B	F_{1B}	Voltage gain at 10-MHz frequency.	-0.6	-0.1	0.4	dB
5	S2 frequency characteristics	F_{2A}	E1, E2 and E3: 5 V.	-0.6	-0.1	0.4	dB
6	2A, 2B	F_{2B}	2-k Ω load connected to output pin.	-0.6	-0.1	0.4	dB
7	S3 frequency characteristics	F_{3A}		-0.6	-0.1	0.4	dB
8	3A, 3B	F_{3B}		-0.6	-0.1	0.4	dB
9	S1 voltage gain	G_{1A}	Input: 0.5-Vpp sine wave (SG1)	-0.6	-0.1	0.4	dB
10	1A, 1B	G_{1B}	Voltage gain at 1-MHz frequency	-0.6	-0.1	0.4	dB
11	S2 voltage gain 2A,	G_{2A}	E1, E2 and E3: 5 V	-0.6	-0.1	0.4	dB
12	2B	G_{2B}		-0.6	-0.1	0.4	dB
13	S3 voltage gain	G_{3A}		-0.6	-0.1	0.4	dB
14	3A, 3B	G_{3B}		-0.6	-0.1	0.4	dB
15	S1 input bias voltage	$V_{IDC 1A}$	No signal input.	4.1	4.6	5.1	V
16	1A, 1B	$V_{IDC 1B}$	DC voltage at input pin.	4.1	4.6	5.1	V
17	S2 input bias voltage	$V_{IDC 2A}$		4.1	4.6	5.1	V
18	2A, 2B	$V_{IDC 2B}$		4.1	4.6	5.1	V
19	S3 input bias voltage	$V_{IDC 3A}$		4.1	4.6	5.1	V
20	3A, 3B	$V_{IDC 3B}$		4.1	4.6	5.1	V
21	S1 output bias voltage	$V_{ODC 1}$	No signal input.	3.05	3.2	3.35	V
22	S2 output bias voltage	$V_{ODC 2}$	DC voltage at output pin.	3.05	3.2	3.35	V
23	S3 output bias voltage	$V_{ODC 3}$	Pins 2, 7 and 12 connected to GND.	3.05	3.2	3.35	V
24	Current flow into control pins	$I_{IN 11}$	Current flow into each of pins 2,	0.35	0.6	1	mA
25	1: S1, S2, S3	$I_{IN 12}$	7 and 12 when these pin voltage is 9 V.	0.35	0.6	1	mA
26		$I_{IN 13}$		0.35	0.6	1	mA
27	Current flow into control pins	$I_{IN 21}$	Current flow into each of pins 2,	0	1.5	10	μ A
28	2: S1, S2, S3	$I_{IN 22}$	7 and 12 when these pin voltage is 5 V.	0	1.5	10	μ A
29		$I_{IN 23}$		0	1.5	10	μ A
30	Current flow into control pins	$I_{IN 31}$	Current flow into each of pins 2,	-5	0	2	μ A
31	3: S1, S2, S3	$I_{IN 32}$	7 and 12 when these pin voltage is 0 V.	-5	0	2	μ A
32		$I_{IN 33}$		-5	0	2	μ A
33a	Threshold voltage S1,	V_{IC1L}	Input: 0.5-Vpp sine wave, $f = 1$	1.7	—	2.7	V
33b	S2,	V_{IC1H}	MHz (SG1). ^{*1 *2}	1.7	—	2.7	V
34a		V_{IC2L}		1.7	—	2.7	V
34b	S3	V_{IC2H}		1.7	—	2.7	V
35a		V_{IC3L}		1.7	—	2.7	V
35b		V_{IC3H}		1.7	—	2.7	V






Electrical Characteristics (cont)

No.	Measurement item	Symbol	Measurement conditions	Limits			Unit
				Min.	Typ.	Max.	
36	S1 2nd harmonic distortion 1A,	H _{1A}	Input: 4.5-Vpp sine wave, f = 5 MHz (SG1).	—	-60	-50	dB
37	1B	H _{1B}		—	-60	-50	
38	S2 2nd harmonic distortion 2A,	H _{2A}	E1, E2 and E3: 5 V Voltage ratio of 10-MHz output element against 5-MHz output element	—	-60	-50	dB
39	2B	H _{2B}		—	-60	-50	
40	S3 2nd harmonic distortion 3A	H _{3A}	2-kΩ load connected to output pin	—	-60	-50	dB
41	S3 2nd harmonic distortion	H _{3B}	Input: 4.5-Vpp sine wave, f = 5 MHz (SG1).	—	-60	-50	dB
42	S1 total harmonic distortion ratio	THD1A	Measure THD with sine wave input of 1 Vrms and f = 5 MHz (SG1).	—	0.05	0.2	%
43	1A, 1B	THD1B		—	0.05	0.2	
44	S2 total harmonic distortion ratio	THD2A	E1, E2 and E3: 5 V.	—	0.05	0.2	%
45	2A, 2B	THD2B		—	0.05	0.2	
46	S3 total harmonic distortion ratio	THD3A		—	0.05	0.2	%
47	3A, 3B	THD3B		—	0.05	0.2	
48	S1 crosstalk	CT11	Input: 0.5-Vpp sine wave, f = 5 MHz (SG1).	—	-70	-60	dB
49	1B-1A, 1A-1B	CT12		—	-70	-60	
50	S2 crosstalk	CT21	Voltage ratio of non-input-side output against input-side output when the non-input-side pin is connected to GND with 0.01 μF.	—	-70	-60	dB
51	2B-2A, 2A-2B	CT22		—	-70	-60	
52	S3 crosstalk	CT31	E1, E2 and E3: 5 V	—	-70	-60	dB
53	3B-3A, 3A-3B	CT32		—	-70	-60	
54	S1 crosstalk between channels	CT13	Input: 0.5-Vpp sine wave, f = 5 MHz (SG1).	—	-70	-60	dB
55	2A-1A, 2B-1A, 3A-1A, 3B-1A	CT14		—	-70	-60	
56		CT15	Voltage ratio of no-input-side output against input-side output when no-input-side pin is connected to GND with 0.01 μF.	—	-70	-60	dB
57		CT16		—	-70	-60	
58	2A-1B,	CT17	E1, E2 and E3: 5 V	—	-70	-60	dB
59	2B-1B,	CT18		—	-70	-60	
60	3A-1B,	CT19		—	-70	-60	
61	3B-1B	CT1A		—	-70	-60	
62	S2 crosstalk between channels	CT23		—	-70	-60	dB
63	1A-2A, 1B-2A, 3A-2A, 3B-2A	CT24		—	-70	-60	dB
64		CT25		—	-70	-60	dB
65		CT26		—	-70	-60	dB
66	1A-2B,	CT27		—	-70	-60	dB
67	1B-2B,	CT28		—	-70	-60	dB
68	3A-2B,	CT29		—	-70	-60	dB
69	3B-2B	CT2A		—	-70	-60	dB
70	S3 crosstalk between channels	CT33		—	-70	-60	dB
71	1A-3A, 1B-3A, 2A-3A, 2B-3A	CT34		—	-70	-60	dB
72		CT35		—	-70	-60	dB
73		CT36		—	-70	-60	dB
74	1A-3B,	CT37		—	-70	-60	dB
75	1B-3B,	CT38		—	-70	-60	dB
76	2A-3B,	CT39		—	-70	-60	dB
77	2B-3B	CT3A		—	-70	-60	dB

Electrical Characteristics (cont)


No.	Measurement item	Symbol	Measurement conditions	Limits			Unit
				Min.	Typ.	Max.	
78	S1 output DC offset voltage	V_{OS1}	No signal input. E1, E2 and E3: 5 V.	-10	0	10	mV
79	S2 output DC offset voltage	V_{OS2}	DC voltage difference in output.* ³	-10	0	10	mV
80	S3 output DC offset voltage	V_{OS3}		-10	0	10	mV
81a	Threshold voltage ($V_{CC} = 5\text{ V}$)	V_{IC4L}	Input: 0.5-Vp-p sine wave, $f = 1$	1.3	—	2.3	V
81b	S1, S2, S3	V_{IC4H}	MHz (SG1).	1.3	—	2.3	V
82a		V_{IC5L}	$V_{CC} = 5\text{ V}$. ^{*4 *5}	1.3	—	2.3	V
82b		V_{IC5H}		1.3	—	2.3	V
83a		V_{IC6L}		1.3	—	2.3	V
83b		V_{IC6H}		1.3	—	2.3	V
84a	Threshold voltage ($V_{CC} = 12\text{ V}$)	V_{IC7L}	Input: 0.5-Vp-p sine wave, $f = 1$	2.0	—	3.0	V
84b	S1, S2, S3	V_{IC7H}	MHz (SG1).	2.0	—	3.0	V
85a		V_{IC8L}	$V_{CC} = 12\text{ V}$. ^{*6 *7}	2.0	—	3.0	V
85b		V_{IC8H}		2.0	—	3.0	V
86a		V_{IC9L}		2.0	—	3.0	V
86b		V_{IC9H}		2.0	—	3.0	V

Typical Characteristics



Method to Measure Electric Characteristics

1. Measurement Circuit



2 Measurement Conditions

No.	Symbol	Switch status												Point to be measured
		S1	S2	S3	S4	S5	S6	S7	S8	S9	S10	S11	S12	
1	I _{CC1}	a	a	a	d	b	b							A ₁
2	I _{CC2}	a	a	a	d	b	b							A ₁
3	F _{1A}	a			a		a	b	b	b	b	b	a	V ₁
4	F _{1B}	b			a	a		a	b	b	b	b	b	V ₁
5	F _{2A}		a		b		a	b	b	b	a	b	b	V ₂
6	F _{2B}		b		b	a		b	b	b	b	a	b	V ₂
7	F _{3A}			a	c		a	b	a	b	b	b	b	V ₃
8	F _{3B}			b	c	a		b	b	a	b	b	b	V ₃
9	G _{1A}	a			d		a	b	b	b	b	b	a	V ₁
10	G _{1B}	b			d	a		a	b	b	b	b	b	V ₁
11	G _{2A}		a		d		a	b	b	b	a	b	b	V ₂
12	G _{2B}		b		d	a		b	b	b	b	a	b	V ₂
13	G _{3A}			a	d		a	b	a	b	b	b	b	V ₃
14	G _{3B}			b	d	a		b	b	a	b	b	b	V ₃
15	V _{IDC 1A}	a			d	b	b	a	a	a	a	a	b	V ₄
16	V _{IDC 1B}	a			d	b	b	b	a	a	a	a	a	V ₄
17	V _{IDC 2A}		a		d	b	b	a	a	a	b	a	a	V ₄
18	V _{IDC 2B}		a		d	b	b	a	a	a	a	b	a	V ₄
19	V _{IDC 3A}			a	d	b	b	a	b	a	a	a	a	V ₄
20	V _{IDC 3B}			a	d	b	b	a	a	b	a	a	a	V ₄
21	V _{ODC 1}	a			d	b	b	a	b	b	b	b	a	V ₁
22	V _{ODC 2}		a		d	b	b	b	b	b	a	a	b	V ₂
23	V _{ODC 3}			a	d	b	b	b	a	a	b	b	b	V ₃
24	I _{IN 11}	b			d	b	b							A ₂
25	I _{IN 12}		b		d	b	b							A ₃
26	I _{IN 13}			b	d	b	b							A ₄
27	I _{IN 21}	b			d	b	b							A ₂
28	I _{IN 22}		b		d	b	b							A ₃
29	I _{IN 23}			b	d	b	b							A ₄
30	I _{IN 31}	a			d	b	b							A ₂
31	I _{IN 32}		a		d	b	b							A ₃
32	I _{IN 33}			a	d	b	b							A ₄
33a	V _{IC1L}	b			d	b	a	b	b	b	b	b	a	E ₁ ^{Note1}
33b	V _{IC1H}					a	b	a					b	E ₁ ^{Note2}
34a	V _{IC2L}		b		d	b	a	b	b	b	a	b	b	E ₂ ^{Note1}
34b	V _{IC2H}					a	b				b	a		E ₂ ^{Note2}
35a	V _{IC3L}			b	d	b	a	b	a	b	b	b	b	E ₃ ^{Note1}
35b	V _{IC3H}					a	b		b	a				E ₃ ^{Note2}
36	H _{1A}	a			a	b	a	b	b	b	b	b	a	V ₁
37	H _{1B}	b			a	a	b	a	b	b	b	b	b	V ₁
38	H _{2A}		a		b	b	a	b	b	b	a	b	b	V ₂
39	H _{2B}		b		b	a	b	b	b	b	b	a	b	V ₂
40	H _{3A}			a	c	b	a	b	a	b	b	b	b	V ₃
41	H _{3B}			b	c	a	b	b	b	a	b	b	b	V ₃

Measurement Conditions (cont)


No.	Symbol	Switch status												Point to be measured
		S1	S2	S3	S4	S5	S6	S7	S8	S9	S10	S11	S12	
42	THD1A	a			d	b	a	b	b	b	b	b	a	V ₁
43	THD1B	b			d	a	b	a	b	b	b	b	b	V ₁
44	THD2A		a		d	b	a	b	b	b	a	b	b	V ₂
45	THD2B		b		d	a	b	b	b	b	b	a	b	V ₂
46	THD3A			a	d	b	a	b	a	b	b	b	b	V ₃
47	THD3B			b	d	a	b	b	b	a	b	b	b	V ₃
48	CT11	a			a	a	b	a	b	b	b	b	a	V ₁
49	CT12	b			a	b	a	a	b	b	b	b	a	V ₁
50	CT21		a		b	a	b	b	b	b	a	a	b	V ₂
51	CT22		b		b	b	a	b	b	b	a	a	b	V ₂
52	CT31			a	c	a	b	b	a	a	b	b	b	V ₃
53	CT32			b	c	b	a	b	a	a	b	b	b	V ₃
54	CT13	a	b		a	b	a	b	b	b	a	b	b	V ₁
55	CT14	a	a		a	a	b	b	b	b	b	a	b	V ₁
56	CT15	a		b	a	b	a	b	a	b	b	b	b	V ₁
57	CT16	a		a	a	a	b	b	b	a	b	b	b	V ₁
58	CT17	b	b		a	b	a	b	b	b	a	b	b	V ₁
59	CT18	b	a		a	a	b	b	b	b	b	a	b	V ₁
60	CT19	b		b	a	b	a	b	a	b	b	b	b	V ₁
61	CT1A	b		a	a	a	b	b	b	a	b	b	b	V ₁
62	CT23	b	a		b	b	a	b	b	b	b	b	a	V ₂
63	CT24	a	a		b	a	b	a	b	b	b	b	b	V ₂
64	CT25		a	b	b	b	a	b	a	b	b	b	b	V ₂
65	CT26		a	a	b	a	b	b	b	a	b	b	b	V ₂
66	CT27	b	b		b	b	a	b	b	b	b	b	a	V ₂
67	CT28	a	b		b	a	b	a	b	b	b	b	b	V ₂
68	CT29		b	b	b	b	a	b	a	b	b	b	b	V ₂
69	CT2A		b	a	b	a	b	b	b	a	b	b	b	V ₂
70	CT33	b		a	c	b	a	b	b	b	b	b	a	V ₃
71	CT34	a		a	c	a	b	a	b	b	b	b	b	V ₃
72	CT35		b	a	c	b	a	b	b	b	a	b	b	V ₃
73	CT36		a	a	c	a	b	b	b	b	b	a	b	V ₃
74	CT37	b		b	c	b	a	b	b	b	b	b	a	V ₃
75	CT38	a		b	c	a	b	a	b	b	b	b	b	V ₃
76	CT39		b	b	c	b	a	b	b	b	a	b	b	V ₃
77	CT3A		a	b	c	a	b	b	b	b	b	a	b	V ₃
78	V _{os1}	a			d	b	b	a	b	b	b	b	a	V ₁ ^{Note3}
		b												
79	V _{os2}		a		d	b	b	b	b	b	a	a	b	V ₂ ^{Note3}
			b											
80	V _{os3}			a	d	b	b	b	a	a	b	b	b	V ₃ ^{Note3}
				b										

Measurement Conditions (cont)

No.	Symbol	Switch status												Point to be measured
		S1	S2	S3	S4	S5	S6	S7	S8	S9	S10	S11	S12	
81a	V _{IC4L}	b			d	b	a	b	b	b	b	b	a	E ₁ ^{Note4}
81b	V _{IC4H}					a	b	a					b	E ₁ ^{Note5}
82a	V _{IC5L}		b		d	b	a	b	b	b	a	b	b	E ₂ ^{Note4}
82b	V _{IC5H}					a	b				b	a		E ₂ ^{Note5}
83a	V _{IC6L}			b	d	b	a	b	a	b	b	b	b	E ₃ ^{Note4}
83b	V _{IC6H}					a	b		b	a				E ₃ ^{Note5}
84a	V _{IC7L}	b			d	b	a	b	b	b	b	b	a	E ₁ ^{Note6}
84b	V _{IC7H}					a	b	a					b	E ₁ ^{Note7}
85a	V _{IC8L}		b		d	b	a	b	b	b	a	b	b	E ₂ ^{Note6}
85b	V _{IC8H}					a	b				b	a		E ₂ ^{Note7}
86a	V _{IC9L}			b	d	b	a	b	a	b	b	b	b	E ₃ ^{Note6}
86b	V _{IC9H}					a	b		b	a				E ₃ ^{Note7}


- Notes:
- For V_{IC1L}, V_{IC2L} and V_{IC3L}, respectively read the E₁, E₂ and E₃ voltage when their output amplitudes are 0.5 dB smaller than those of V₁, V₂ and V₃ in measuring G_{1A} in No. 9, G_{2A} in No. 11 and G_{3A} in No. 13.
 - For V_{IC1H}, V_{IC2H} and V_{IC3H}, respectively read the E₁, E₂ and E₃ voltage when their output amplitudes are 0.5 dB smaller than those of V₁, V₂ and V₃ in measuring G_{1B} in No. 10, G_{2B} in No. 12 and G_{3B} in No. 14.
 - Read the potential difference "V_{OS}" = V_H - V_L, where V_L indicates output voltage when the control voltage is 0 V and V_H indicates output voltage when the control voltage is 5 V.
 - V_{CC} = 5 V.
For V_{IC4L}, V_{IC5L} and V_{IC6L}, respectively read the E₁, E₂ and E₃ voltage when their output amplitudes are 1.0 dB smaller than those of V₁, V₂ and V₃ in measuring G_{1A} in No. 9, G_{2A} in No. 11 and G_{3A} in No. 13.
 - V_{CC} = 5 V.
For V_{IC4H}, V_{IC5H} and V_{IC6H}, respectively read the E₁, E₂ and E₃ voltage when their output amplitudes are 1.0 dB smaller than those of V₁, V₂ and V₃ in measuring G_{1B} in No. 10, G_{2B} in No. 12 and G_{3B} in No. 14.
 - Same as 4 above except V_{CC} = 12 V.
 - Same as 5 above except V_{CC} = 12 V.

Application Example



USAGE NOTES

1. The input impedance is 20 k Ω (standard value).
2. Output drive current should be 5 mA or less when using this IC.
3. Note that voltage applied to the control pins (pins 2, 7 and 12) should be less than the power supply voltage (Vcc) and more than the ground voltage (GND). The following shows an internal equivalent circuit coupled to a control pin.



4. Output pins are the emitter follower type. The following drive current is applied inside the IC normally. If the drive performance is insufficient, apply external drive current within the range shown in 2.

Power supply voltage (Vcc)	Drive current in the IC (standard value)
5 V	190 μ A
9V	380 μ A
12 V	530 μ A




Package Dimensions

Plastic 16pin 300mil DIP

(MMP)

16P4

EIAJ Package Code DIP16-P-300-2.54	JEDEC Code -	Weight(g) 1.0	Lead Material Alloy 42/Cu Alloy
---------------------------------------	-----------------	------------------	------------------------------------



Symbol	Dimension in Millimeters		
	Min	Nom	Max
A	-	-	4.5
A1	0.51	-	-
A2	-	3.3	-
b	0.4	0.5	0.59
b1	1.4	1.5	1.8
b2	0.9	1.0	1.3
c	0.22	0.27	0.34
D	18.8	19.0	19.2
E	6.15	6.3	6.45
e	-	2.5	-
ei	-	7.62	-
L	3.0	-	-
θ	0°	-	15°

Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.



RENESAS SALES OFFICES

<http://www.renesas.com>

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500 Fax: <1> (408) 382-7501

Renesas Technology Europe Limited.
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, United Kingdom
Tel: <44> (1628) 585 100, Fax: <44> (1628) 585 900

Renesas Technology Europe GmbH
Dornacher Str. 3, D-85622 Feldkirchen, Germany
Tel: <49> (89) 380 70 0, Fax: <49> (89) 929 30 11

Renesas Technology Hong Kong Ltd.
7/F., North Tower, World Finance Centre, Harbour City, Canton Road, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2375-6836

Renesas Technology Taiwan Co., Ltd.
FL 10, #99, Fu-Hsing N. Rd., Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd.
26/F., Ruijin Building, No.205 Maoming Road (S), Shanghai 200020, China
Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

Renesas Technology Singapore Pte. Ltd.
1, Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001